



Application:

This system is recommended for every 3D-Thermoformer, and is used for cutting the foils near the press. The system is available in a Single-version or in combination with a foils-storage-rack.

Working procedure

Version 1 - the Single-Cutter-System for Serial-manufacturer

From the integrated foil rack (2 hangers) the foils will be pulled by hand through the Single-Cutter-System, and at a touch of a button the foils will be cut-off. Simultaneously the foil will be pulled-up app. 6 ´´(=15 cm) automatically (for easy access to the next charge).

Version 2 - the Cutter-System in combination with a foils-rack- for multiple roll change.

The chosen foils will be pulled-in by hand directly from the rack through the cutter on the pressshuttle and at a touch of a button the foils will be cut-off. Simultaneously the foil will be pulled-up app. 6 ((=15 cm)) automatically (for easy access for the next charge).



Option: Ionization system

